

Garant**Eco toolholder axial double, right-hand, HSK-T 63, for toolholder square: 25mm****Order data**

| | |
|--------------|---------------|
| Order number | 318623 25 |
| GTIN | 4045197893253 |
| Item class | 31G |

Description**Version:**

With adjustable cooling nozzle with internal thread.

GARANT - Optimisation of tool life, better surface finishes, increased process reliability and increased productivity due to GARANT Eco.

Application:

For use on lathes and milling centres.

For mounting ISO toolholders with square shanks.

Note:

With pass-through shim. Suitable for toolholders with shank 20 **and** 25 mm.

Technical description

| | |
|--------------------------------|-------------|
| for toolholder square | 25 mm |
| Clamping length L ₁ | 88 mm |
| B | 40 mm |
| Overhang dimension A | 130 mm |
| External Ø D | 102 mm |
| Adapter | HSK-T 63 |
| Arbor standard | ISO 12164-3 |

| | |
|-----------------|----------|
| Through-coolant | yes |
| Type of product | Pin vice |