

Garant**Eco toolholder diagonal 45°, right-hand, PSC 63, for toolholder square: 25mm**

Order data

Order number	318857 25
GTIN	4045197893338
Item class	31G

Description

Version:

With adjustable cooling nozzle with internal thread.

GARANT - Optimisation of tool life, better surface finishes, increased process reliability and increased productivity due to GARANT Eco.

Application:

For use on lathes and milling centres.

For mounting ISO toolholders with square shanks.

Note:

PSC clamping stud on request. With pass-through shim. Suitable for toolholders with shank 20 and 25 mm.

Technical description

Tip centre offset f	12.7 mm
Overhang dimension A	110 mm
External Ø D	94 mm
for toolholder square	25 mm
B	40 mm
Adapter	PSC 63
Arbor standard	ISO 26623-2

Through-coolant	yes
Type of product	Pin vice