

Garant

**Steel boring bar A.. SDQCR 107,5°, for indexable inserts DC., right-hand,
Shank Ø / insert size: 10/07mm**


Order data

Order number	260340 10/07
GTIN	4045197877796
Item class	21T

Technical description

Clamping height L_2	9 mm
Overall length L	125 mm
suitable indexable insert	DC.. 0702..
ISO code toolholder	A10K SDQCR/L07
Minimum pre-drill $\varnothing D_{\min}$	14 mm
Insert size	7 mm
Centre offset L_3	7 mm
Overhang L_1	30 mm
Setting angle κ	107.5 degrees
Pack of insert screws	269028 7
Shank $\varnothing D_s$	10 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8