

**Garant**

**Steel boring bar A.. SDQCR 107,5°, for indexable inserts DC., right-hand,  
Shank Ø / insert size: 20/11mm**


**Order data**

|              |               |
|--------------|---------------|
| Order number | 260340 20/11  |
| GTIN         | 4045197877826 |
| Item class   | 21T           |

**Technical description**

|                                      |                               |
|--------------------------------------|-------------------------------|
| suitable indexable insert            | DC.. 11T3..                   |
| Overall length L                     | 200 mm                        |
| Pack of insert screws                | 269028 8                      |
| Centre offset L <sub>3</sub>         | 13 mm                         |
| Minimum pre-drill Ø D <sub>min</sub> | 26 mm                         |
| Clamping height L <sub>2</sub>       | 18 mm                         |
| Overhang L <sub>1</sub>              | 60 mm                         |
| ISO code toolholder                  | A20R SDQCR/L11                |
| Insert size                          | 11 mm                         |
| Setting angle κ                      | 107.5 degrees                 |
| Shank Ø D <sub>s</sub>               | 20 mm                         |
| Standard                             | DIN 8024                      |
| Application type                     | right-hand                    |
| Boring depth up to                   | 3×D                           |
| Through-coolant                      | yes                           |
| Application                          | Internal longitudinal turning |

Type of product

Boring Bar

---

**Accessories**

Set of insert screws Type 8

269028 8

Torque screwdriver with scale, to take interchangeable  
blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15