

Garant

Steel boring bar A.. SDQCL 107,5°, for indexable inserts DC.., left-hand, Shank Ø / insert size: 12/07mm


Order data

| | |
|--------------|---------------|
| Order number | 260341 12/07 |
| GTIN | 4045197877871 |
| Item class | 21T |

Technical description

| | |
|--|-------------------------------|
| Overhang L_1 | 36 mm |
| Overall length L | 140 mm |
| Centre offset L_3 | 9 mm |
| Insert size | 7 mm |
| Pack of insert screws | 269028 7 |
| ISO code toolholder | A12L SDQCR/L07 |
| Minimum pre-drill $\varnothing D_{\min}$ | 17 mm |
| Setting angle κ | 107.5 degrees |
| suitable indexable insert | DC.. 0702.. |
| Clamping height L_2 | 11 mm |
| Shank $\varnothing D_s$ | 12 mm |
| Standard | Works standard |
| Application type | left-hand |
| Boring depth up to | 3xD |
| Through-coolant | yes |
| Application | Internal longitudinal turning |

| | |
|-----------------|------------|
| Type of product | Boring Bar |
|-----------------|------------|

Accessories

| | |
|--|------------|
| Set of insert screws Type 7 | 269028 7 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8 | 674248 TX8 |