

Garant

Steel boring bar A.. SDQCL 107,5°, for indexable inserts DC.., left-hand, Shank Ø / insert size: 16/07mm



Order data

Order number	260341 16/07
GTIN	4045197877888
Item class	21T

Technical description

Overall length L	180 mm
Insert size	7 mm
ISO code toolholder	A16Q SDQCR/L07
Minimum pre-drill Ø D _{min}	22 mm
Centre offset L ₃	11 mm
Pack of insert screws	269028 7
Setting angle κ	107.5 degrees
Clamping height L ₂	14 mm
Overhang L ₁	48 mm
suitable indexable insert	DC.. 0702..
Shank Ø D _s	16 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar

Accessories

Set of insert screws Type 7

269028 7

Torque screwdriver with scale, to take interchangeable
blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8