

Garant

Steel boring bar A.. SDQCL 107,5°, for indexable inserts DC.., left-hand, Shank Ø / insert size: 20/11mm


Order data

Order number	260341 20/11
GTIN	4045197877895
Item class	21T

Technical description

Overhang L_1	60 mm
Pack of insert screws	269028 8
Insert size	11 mm
ISO code toolholder	A20R SDQCR/L11
Centre offset L_3	13 mm
Overall length L	200 mm
suitable indexable insert	DC.. 11T3..
Clamping height L_2	18 mm
Minimum pre-drill $\varnothing D_{\min}$	26 mm
Setting angle κ	107.5 degrees
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

Accessories

Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15