

**Garant**

**Steel boring bar A.. SDQCL 107,5°, for indexable inserts DC.., left-hand, Shank Ø / insert size: 40/11mm**


**Order data**

Order number	260341 40/11
GTIN	4045197877925
Item class	21T

**Technical description**

ISO code toolholder	A40T SDQCR/L11
Setting angle $\kappa$	107.5 degrees
Centre offset $L_3$	27 mm
Minimum pre-drill $\varnothing D_{\min}$	49 mm
Shim	269005 3
Overhang $L_1$	120 mm
suitable indexable insert	DC.. 11T3..
Clamping height $L_2$	39 mm
Overall length $L$	300 mm
Shim screw	269013 2
Pack of insert screws	269028 2
Insert size	11 mm
Shank $\varnothing D_s$	40 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Shim Type 3	269005 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15