

Garant

Steel boring bar A.. SDXCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 12/07mm


Order data

Order number	260344 12/07
GTIN	4045197877932
Item class	21T

Technical description

suitable indexable insert	DC.. 0702..
Setting angle κ	93 degrees
Head length L_1	25 mm
Clamping height L_2	11 mm
ISO code toolholder	A12L SDXCR/L07
Pack of insert screws	269028 7
Centre offset L_3	9 mm
Insert size	7 mm
Overall length L	140 mm
Minimum pre-drill $\varnothing D_{\min}$	17 mm
Usable depth T	4.3 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8