

Garant

Steel boring bar A.. SDXCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 16/07mm


Order data

Order number	260344 16/07
GTIN	4045197877949
Item class	21T

Technical description

suitable indexable insert	DC.. 0702..
Overall length L	180 mm
Centre offset L ₃	11 mm
Setting angle κ	93 degrees
Pack of insert screws	269028 7
Head length L ₁	33 mm
Insert size	7 mm
Minimum pre-drill Ø D _{min}	21 mm
ISO code toolholder	A16Q SDXCR/L07
Clamping height L ₂	15 mm
Usable depth T	4.3 mm
Shank Ø D _s	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8