

Garant

Steel boring bar A.. SDXCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 20/11mm


Order data

Order number	260344 20/11
GTIN	4045197877956
Item class	21T

Technical description

Minimum pre-drill Ø D _{min}	25 mm
suitable indexable insert	DC.. 11T3..
Pack of insert screws	269028 8
ISO code toolholder	A20R SDXCR/L11
Head length L ₁	40 mm
Clamping height L ₂	18 mm
Insert size	11 mm
Overall length L	200 mm
Centre offset L ₃	13 mm
Setting angle κ	93 degrees
Usable depth T	10 mm
Shank Ø D _s	20 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15