

Garant

Steel boring bar A.. SDXCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 25/11mm



Order data

Order number	260344 25/11
GTIN	4045197877963
Item class	21T

Technical description

ISO code toolholder	A25R SDXCR/L11
Clamping height L_2	23 mm
Setting angle κ	93 degrees
Centre offset L_3	17 mm
Pack of insert screws	269028 8
suitable indexable insert	DC.. 11T3..
Minimum pre-drill $\varnothing D_{\min}$	31.5 mm
Overall length L	200 mm
Insert size	11 mm
Head length L_1	50 mm
Usable depth T	10 mm
Shank $\varnothing D_s$	25 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15