

**Garant**

**Steel boring bar A.. SDXCL 93°, for indexable inserts DC.., left-hand, Shank Ø / insert size: 12/07mm**


**Order data**

Order number	260345 12/07
GTIN	4045197877970
Item class	21T

**Technical description**

Minimum pre-drill Ø $D_{min}$	17 mm
suitable indexable insert	DC.. 0702..
Centre offset $L_3$	9 mm
Pack of insert screws	269028 7
Head length $L_1$	25 mm
Setting angle $\kappa$	93 degrees
Insert size	7 mm
Overall length L	140 mm
ISO code toolholder	A12L SDXCR/L07
Clamping height $L_2$	11 mm
Usable depth T	4.3 mm
Shank Ø $D_s$	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8