

Garant

Steel boring bar A.. SDXCL 93°, for indexable inserts DC.., left-hand, Shank Ø / insert size: 16/07mm


Order data

Order number	260345 16/07
GTIN	4045197877987
Item class	21T

Technical description

suitable indexable insert	DC.. 0702..
Centre offset L_3	11 mm
Pack of insert screws	269028 7
ISO code toolholder	A16Q SDXCR/L07
Head length L_1	33 mm
Setting angle κ	93 degrees
Insert size	7 mm
Minimum pre-drill $\varnothing D_{\min}$	21 mm
Clamping height L_2	15 mm
Overall length L	180 mm
Usable depth T	4.3 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8