

Garant

Steel boring bar A.. SDXCL 93°, for indexable inserts DC.., left-hand, Shank Ø / insert size: 20/11mm


Order data

Order number	260345 20/11
GTIN	4045197877994
Item class	21T

Technical description

Pack of insert screws	269028 8
Centre offset L_3	13 mm
Clamping height L_2	18 mm
suitable indexable insert	DC.. 11T3..
Insert size	11 mm
Head length L_1	40 mm
Setting angle κ	93 degrees
ISO code toolholder	A20R SDXCR/L11
Overall length L	200 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Usable depth T	10 mm
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15