

**Garant**

**Steel boring bar A.. SDXCL 93°, for indexable inserts DC.., left-hand, Shank Ø / insert size: 25/11mm**


**Order data**

Order number	260345 25/11
GTIN	4045197878007
Item class	21T

**Technical description**

Insert size	11 mm
Setting angle $\kappa$	93 degrees
Overall length L	200 mm
Centre offset $L_3$	17 mm
Minimum pre-drill $\varnothing D_{\min}$	31.5 mm
Clamping height $L_2$	23 mm
Pack of insert screws	269028 8
Head length $L_1$	50 mm
suitable indexable insert	DC.. 11T3..
ISO code toolholder	A25R SDXCR/L11
Usable depth T	10 mm
Shank $\varnothing D_s$	25 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15