

Garant

Steel boring bar A.. SVUBR 93°, for indexable inserts VB.., right-hand, Shank Ø / insert size: 16/11mm


Order data

Order number	261132 16/11
GTIN	4045197878014
Item class	21T

Technical description

Head length L_1	16.5 mm
Centre offset L_3	11 mm
Pack of insert screws	269028 7
Setting angle κ	93 degrees
suitable indexable insert	VB.. 1103..
Overall length L	180 mm
Minimum pre-drill $\varnothing D_{\min}$	21 mm
Clamping height L_2	15.5 mm
Insert size	11 mm
ISO code toolholder	A16Q SVUBR/L11
Shank $\varnothing D_s$	16 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8