

**Garant**

**Steel boring bar A.. SVUBL 93°, for indexable inserts VB.., left-hand, Shank Ø / insert size: 25/16mm**


**Order data**

Order number	261133 25/16
GTIN	4045197878083
Item class	21T

**Technical description**

Setting angle $\kappa$	93 degrees
ISO code toolholder	A25R SVUBR/L16
Clamping height $L_2$	24 mm
Insert size	16 mm
Centre offset $L_3$	17 mm
suitable indexable insert	VB.. 1604..
Overall length L	200 mm
Head length $L_1$	25.5 mm
Pack of insert screws	269028 8
Minimum pre-drill $\varnothing D_{\min}$	32 mm
Shank $\varnothing D_s$	25 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

---

## Accessories

Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15