

Garant

Steel boring bar A.. SVUBL 93°, for indexable inserts VB.., left-hand, Shank Ø / insert size: 40/16mm


Order data

Order number	261133 40/16
GTIN	4045197878106
Item class	21T

Technical description

suitable indexable insert	VB.. 1604..
Head length L_1	40 mm
Centre offset L_3	27 mm
Shim screw	269013 2
Setting angle κ	93 degrees
Shim	269005 8
Pack of insert screws	269028 2
Insert size	16 mm
Minimum pre-drill $\varnothing D_{\min}$	49 mm
Clamping height L_2	39 mm
Overall length L	300 mm
ISO code toolholder	A40T SVUBR/L16
Shank $\varnothing D_s$	40 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Shim Type 8	269005 8
Shim screw Type 2	269013 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15