

**Garant**

**Clamping toolholder SDNCN 62,5°, for indexable inserts DC., neutral, Shank / insert size: 12/07mm**



## Order data

Order number	260300 12/07
GTIN	4045197878243
Item class	21T

## Technical description

Overhang L <sub>1</sub> neutral holders	11 mm
Pack of insert screws	269028 22
ISO code toolholder	SDNCN 1212F07
Insert size	7 mm
Shank size	12 mm
Functional width L <sub>4</sub> neutral holders	6 mm
suitable indexable insert	DC.. 0702..
Overall length L neutral holders	80 mm
Standard	DIN ISO 5610
Application type	neutral
Through-coolant	no
Setting angle κ	62.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar
-----------------	------------

---

## Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15