

Garant

Clamping toolholder SDNCN 62,5°, for indexable inserts DC., neutral, Shank / insert size: 16/11mm



Order data

Order number	260300 16/11
GTIN	4045197878250
Item class	21T

Technical description

Insert size	11 mm
Shim	269005 3
Shim screw	269013 2
Overall length L neutral holders	100 mm
Functional width L ₄ neutral holders	8 mm
Pack of insert screws	269028 2
Overhang L ₁ neutral holders	16 mm
suitable indexable insert	DC.. 11T3..
Shank size	16 mm
ISO code toolholder	SDNCN 1616H11
Standard	DIN ISO 5610
Application type	neutral
Through-coolant	no
Setting angle κ	62.5 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 3	269005 3
Shim screw Type 2	269013 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15