

**Garant**

**Clamping toolholder SDNCN 62,5°, for indexable inserts DC., neutral, Shank / insert size: 20/11mm**



## Order data

Order number	260300 20/11
GTIN	4045197878267
Item class	21T

## Technical description

Shim screw	269013 2
Shim	269005 3
Overall length L neutral holders	125 mm
Insert size	11 mm
Functional width L <sub>4</sub> neutral holders	10 mm
suitable indexable insert	DC.. 11T3..
Overhang L <sub>1</sub> neutral holders	20 mm
ISO code toolholder	SDNCN 2020K11
Pack of insert screws	269028 2
Shank size	20 mm
Standard	DIN ISO 5610
Application type	neutral
Through-coolant	no
Setting angle κ	62.5 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim Type 3	269005 3
Shim screw Type 2	269013 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15