

**Garant**

**Clamping toolholder SDNCN 62,5°, for indexable inserts DC., neutral, Shank / insert size: 25/11mm**



## Order data

Order number	260300 25/11
GTIN	4045197878274
Item class	21T

## Technical description

ISO code toolholder	SDNCN 2525M11
Shim	269005 3
Pack of insert screws	269028 2
Functional width L <sub>4</sub> neutral holders	12.5 mm
Shank size	25 mm
suitable indexable insert	DC.. 11T3..
Overall length L neutral holders	150 mm
Insert size	11 mm
Shim screw	269013 2
Overhang L <sub>1</sub> neutral holders	25 mm
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle κ	62.5 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim Type 3	269005 3
Shim screw Type 2	269013 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15