



Boring bar set, steel, without IC, right-hand, Type: SET06



Order data

Order number	260038 SET06
GTIN	4045197878281
Item class	29W

Description

Version:

Without through-coolant feed.

Supplied with:

Plastic case

Technical description

suitable indexable insert	CC.. 0602..
ISO code toolholder	S1012K SCLCR06
ISO code toolholder	S0608H SCLCR06
ISO code toolholder	S0810J SCLCR06
ISO code toolholder	S1216M SCLCR06
Pack of insert screws	269028 7
Head length L ₁	22 mm
Head length L ₁	27 mm

Head length L_1	33 mm
Head length L_1	42 mm
Clamping height L_2	7 mm
Clamping height L_2	9 mm
Clamping height L_2	11 mm
Clamping height L_2	15 mm
Minimum pre-drill $\varnothing D_{\min}$	8 mm
Minimum pre-drill $\varnothing D_{\min}$	11 mm
Minimum pre-drill $\varnothing D_{\min}$	13 mm
Minimum pre-drill $\varnothing D_{\min}$	17 mm
Centre offset L_3	4 mm
Centre offset L_3	6 mm
Centre offset L_3	7 mm
Centre offset L_3	9 mm
Neck width L_4	6 mm
Neck width L_4	8 mm
Neck width L_4	10 mm
Neck width L_4	12 mm
Overall length L	100 mm
Overall length L	110 mm
Overall length L	125 mm
Overall length L	150 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Type of product	Boring bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8