

Garant
Clamping toolholder SSDCN 45°, for indexable inserts SC., neutral, Shank / insert size: 16/12mm

Order data

| | |
|--------------|---------------|
| Order number | 260711 16/12 |
| GTIN | 4045197880802 |
| Item class | 21T |

Technical description

| | |
|---|-------------------------------|
| Insert size | 12 mm |
| Overhang L ₁ neutral holders | 8.7 mm |
| suitable indexable insert | SC.. 1204.. |
| ISO code toolholder | SSDCN 1616H12 |
| Functional width L ₄ neutral holders | 8 mm |
| Shim | 269005 9 |
| Shim screw | 269013 5 |
| Shank size | 16 mm |
| Overall length L neutral holders | 100 mm |
| Pack of insert screws | 269028 20 |
| Standard | Works standard |
| Application type | neutral |
| Through-coolant | no |
| Setting angle κ | 45 degrees |
| Application | External longitudinal turning |

| | |
|-----------------|-------------------------------|
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|-------------|
| Shim Type 9 | 269005 9 |
| Shim screw Type 5 | 269013 5 |
| Set of insert screws Type 20 | 269028 20 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15 | 674248 TX15 |