

Garant
Clamping toolholder SSDCN 45°, for indexable inserts SC., neutral, Shank / insert size: 20/12mm

Order data

Order number	260711 20/12
GTIN	4045197880819
Item class	21T

Technical description

Overall length L neutral holders	125 mm
Pack of insert screws	269028 20
Functional width L ₄ neutral holders	10 mm
Shank size	20 mm
Shim screw	269013 5
Shim	269005 9
ISO code toolholder	SSDCN 2020K12
suitable indexable insert	SC.. 1204..
Overhang L ₁ neutral holders	11.2 mm
Insert size	12 mm
Standard	DIN ISO 5610
Application type	neutral
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 9	269005 9
Shim screw Type 5	269013 5
Set of insert screws Type 20	269028 20
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15