

Garant
Clamping toolholder SSDCN 45°, for indexable inserts SC., neutral, Shank / insert size: 25/12mm

Order data

Order number	260711 25/12
GTIN	4045197880826
Item class	21T

Technical description

ISO code toolholder	SSDCN 2525M12
Functional width L ₄ neutral holders	12.5 mm
suitable indexable insert	SC.. 1204..
Pack of insert screws	269028 20
Shim screw	269013 5
Insert size	12 mm
Shim	269005 9
Overall length L neutral holders	150 mm
Overhang L ₁ neutral holders	13.7 mm
Shank size	25 mm
Standard	DIN ISO 5610
Application type	neutral
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 9	269005 9
Shim screw Type 5	269013 5
Set of insert screws Type 20	269028 20
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15