

HOLEX

**Heavy-duty combination pliers, bright finish, with two-component grips,
Overall length: 200mm**



Order data

Order number	700445 200
GTIN	4045197882332
Item class	72B

Description

Version:

Considerable cutting performance with little effort. Serrated jaws. Cutting edges additionally induction hardened (approx. 63 HRC); suitable even for piano wire. Jaws bright finished, handles with multi-component covering.

Standard:

DIN ISO 5746.

Material:

Special tool steel, drop-forged and oil-hardened.

Technical description

overall length	200 mm
Cutting capacity piano wire up to Ø	2.2 mm
Cutting capacity hard wire up to Ø	2.8 mm
Standard	DIN ISO 5746
Handle	2-component grip
Manufacturing process	Cutting edges induction hardened (approx. 63 HRC)
Material	Special tool steel
Surface	bright finish

non-sparking	no
Type of product	Multi-function pliers