



External micrometer Inch graduations, Measuring range: 0-1in



Order data

Order number	420650 0-1
GTIN	4045197882578
Item class	42B

Description

Version:

With hand temperature protection.

Precision lapped, carbide-tipped measuring faces. Hardened and ground measuring spindle. Locking by locking lever. With ratchet. Precision engraved black divisions and numerals.

Supplied with:

From size 1-2 including 1 setting standard.

Technical description

Spindle Ø	6.5 mm
Calibration	B1
Barrel Ø	18 mm
Scale divisions	0.0001 in
Measuring range	0 - 1 in
Standard	Manufacturer's standard
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External micrometer without setting dimension
maximum measuring range 25 mm

022000 25

DAkkS calibration External micrometer without setting
dimension maximum measuring range 100 mm

022010 100