



External micrometer Inch graduations, Measuring range: 3-4in



Order data

Order number	420650 3-4
GTIN	4045197882707
Item class	42B

Description

Version:

With hand temperature protection.

Precision lapped, carbide-tipped measuring faces. Hardened and ground measuring spindle. Locking by locking lever. With ratchet. Precision engraved black divisions and numerals.

Supplied with:

From size 1-2 including 1 setting standard.

Technical description

Calibration	B2
Barrel Ø	18 mm
Spindle Ø	6.5 mm
Scale divisions	0.0001 in
Measuring range	3 - 4 in
Standard	Manufacturer's standard
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100
DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100

Accessories

Micrometer setting standard overall length 3	421150 3
--	----------