


**Steel gauge block Tolerance class 1, Nominal size: 25mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 481050 25     |
| GTIN         | 4045197210180 |
| Item class   | 42K           |

**Description****Version:**

All gauge blocks are marked with an individual identification number.

Of special alloy steel, carefully hardened and stress-relieved.

Size 0.5 to 10 – cross-section = 30×9 mm.

Size 11 to 500 – cross-section = 35×9 mm.

**Tolerance class 1** for checking standards, gauges and for setting length gauges as well as for normal inspection work in the inspection room.

Version same as No. 480450.

**Note:**

Other nominal dimensions available on request.

**Technical description**

|                 |                                                   |
|-----------------|---------------------------------------------------|
| Nominal size    | 25 mm                                             |
| Standard        | DIN EN ISO 3650                                   |
| Tolerance class | 1                                                 |
| Material        | special alloy steel, hardened and stress-relieved |
| Calibration     | L2                                                |

|                 |             |
|-----------------|-------------|
| Type of product | Gauge block |
|-----------------|-------------|

Services

|                                                              |            |
|--------------------------------------------------------------|------------|
| CalibrationGauge block steel / ceramic maximum length 100 mm | 028060 100 |
| DAkkS calibrationSteel gauge block maximum length 100 mm     | 028140 100 |