



## Double open ended spanner, phosphated, Jaw widths: 41X46mm



### Order data

Order number	610900 41X46
GTIN	4045197384386
Item class	62A

### Description

**Version:**

Drop-forged. With close tolerance jaw widths.  
With oval shank.

**Standard:**

**DIN 3110 / ISO 3318**

**Material:**

Chrome vanadium steel, phosphated.

### Technical description

maximum jaw width b1	88 mm
Width across flats 1	41 mm
maximum jaw width b2	95 mm
maximum jaw height h	12 mm
Width across flats 2	46 mm
Width across flats	metric
Spanner length L	400 mm
Standard	DIN 3110
Standard	ISO 3318
Jaw position 1	15 degrees
Jaw position 2	15 degrees

Surface	phosphated
Product name attribute	phosphated
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner