



Double open ended spanner, phosphated, Jaw widths: 25X28mm



Order data

Order number	610900 25X28
GTIN	4045197384300
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw widths.
With oval shank.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome vanadium steel, phosphated.

Technical description

maximum jaw width b2	62 mm
Width across flats 2	28 mm
maximum jaw height h	9 mm
Width across flats 1	25 mm
maximum jaw width b1	56 mm
Width across flats	metric
Spanner length L	274 mm
Standard	DIN 3110
Standard	ISO 3318
Jaw position 1	15 degrees
Jaw position 2	15 degrees

Surface	phosphated
Product name attribute	phosphated
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner