

**Double open ended spanner set, phosphated, Number of keys: 13****Order data**

|              |               |
|--------------|---------------|
| Order number | 610910 13     |
| GTIN         | 4045197384423 |
| Item class   | 62A           |

**Description****Version:**

Drop-forged. With close tolerance jaw widths.

With oval shaft.

**Standard:**

**DIN 3110 / ISO 3318**

**Material:**

Chrome vanadium steel, phosphated.

**Supplied with:**

1 each double open ended spanner No. 610600 / 610100 / 610900 / 610950 / 610120: Size 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×19; 20×22; 21×23; 24×26; 27×32; 30×34; 36×41

**Technical description**

|                    |            |
|--------------------|------------|
| Number of keys     | 13         |
| Width across flats | metric     |
| Jaw position 1     | 15 degrees |
| Jaw position 2     | 15 degrees |
| Surface            | phosphated |
| Type of product    | Spanner    |

## Accessories

|                                               |              |
|-----------------------------------------------|--------------|
| Double open ended spanner Jaw widths 27X32 mm | 610900 27X32 |
| Double open ended spanner Jaw widths 20X22 mm | 610900 20X22 |
| Double open ended spanner Jaw widths 18X19 mm | 610900 18X19 |
| Double open ended spanner Jaw widths 14X15 mm | 610900 14X15 |
| Double open ended spanner Jaw widths 24X26 mm | 610900 24X26 |
| Double open ended spanner Jaw widths 16X17 mm | 610900 16X17 |
| Double open ended spanner Jaw widths 30X34 mm | 610900 30X34 |
| Double open ended spanner Jaw widths 10X11 mm | 610900 10X11 |
| Double open ended spanner Jaw widths 21X23 mm | 610900 21X23 |
| Double open ended spanner Jaw widths 6X7 mm   | 610900 6X7   |
| Double open ended spanner Jaw widths 12X13 mm | 610900 12X13 |
| Double open ended spanner Jaw widths 36X41 mm | 610900 36X41 |
| Double open ended spanner Jaw widths 8X9 mm   | 610900 8X9   |