

**Double open ended spanner, phosphated, Jaw widths: 7X8mm****Order data**

Order number	610900 7X8
GTIN	4045197384072
Item class	62A

Description**Version:**

Drop-forged. With close tolerance jaw widths.
With oval shank.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome vanadium steel, phosphated.

Technical description

maximum jaw width b1	18 mm
maximum jaw width b2	20 mm
maximum jaw height h	4 mm
Width across flats 1	7 mm
Width across flats 2	8 mm
Width across flats	metric
Spanner length L	130 mm
Standard	DIN 3110
Standard	ISO 3318
Jaw position 1	15 degrees
Jaw position 2	15 degrees

Surface	phosphated
Product name attribute	phosphated
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner