

**Double open ended spanner set, chrome-plated, Number of keys: 13****Order data**

Order number	610960 13
GTIN	4045197459596
Item class	62A

Description**Version:**

Drop-forged. With close tolerance jaw widths.

With oval shaft.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome vanadium steel, chrome-plated.

Supplied with:

1 each double open ended spanner No. 610600 / 610100 / 610900 / 610950 / 610120: Size 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×19; 20×22; 21×23; 24×26; 27×32; 30×34; 36×41

Technical description

Number of keys	13
Width across flats	metric
Jaw position 1	15 degrees
Jaw position 2	15 degrees
Surface	chrome-plated
Type of product	Spanner

Accessories

Double open ended spanner Jaw widths 30X34 mm	610950 30X34
Double open ended spanner Jaw widths 20X22 mm	610950 20X22
Double open ended spanner Jaw widths 8X9 mm	610950 8X9
Double open ended spanner Jaw widths 16X17 mm	610950 16X17
Double open ended spanner Jaw widths 14X15 mm	610950 14X15
Double open ended spanner Jaw widths 10X11 mm	610950 10X11
Double open ended spanner Jaw widths 12X13 mm	610950 12X13
Double open ended spanner Jaw widths 6X7 mm	610950 6X7
Double open ended spanner Jaw widths 24X26 mm	610950 24X26
Double open ended spanner Jaw widths 18X19 mm	610950 18X19
Double open ended spanner Jaw widths 36X41 mm	610950 36X41
Double open ended spanner Jaw widths 21X23 mm	610950 21X23
Double open ended spanner Jaw widths 27X32 mm	610950 27X32