

**Double open ended spanner, chrome-plated, Jaw widths: 21X24mm****Order data**

Order number	610950 21X24
GTIN	4045197159359
Item class	62A

Description**Version:**

Drop-forged. With close tolerance jaw widths.

With oval shaft.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome vanadium steel, chrome-plated.

Technical description

maximum jaw width b1	47 mm
Width across flats 1	21 mm
maximum jaw height h	8 mm
maximum jaw width b2	53 mm
Width across flats 2	24 mm
Width across flats	metric
Spanner length L	245 mm
Standard	DIN 3110
Standard	ISO 3318
Jaw position 1	15 degrees
Jaw position 2	15 degrees

Surface	chrome plated
Product name attribute	chrome-plated
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner