



## Double open ended spanner, chrome-plated, Jaw widths: 32X36mm



### Order data

Order number	610950 32X36
GTIN	4045197441492
Item class	62A

### Description

**Version:**

Drop-forged. With close tolerance jaw widths.  
With oval shaft.

**Standard:**

**DIN 3110 / ISO 3318**

**Material:**

Chrome vanadium steel, chrome-plated.

### Technical description

maximum jaw height h	10 mm
Width across flats 2	36 mm
maximum jaw width b2	80 mm
maximum jaw width b1	70 mm
Width across flats 1	32 mm
Width across flats	metric
Spanner length L	325 mm
Standard	DIN 3110
Standard	ISO 3318
Jaw position 1	15 degrees
Jaw position 2	15 degrees

Surface	chrome plated
Product name attribute	chrome-plated
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner