



Double open ended spanner, chrome-plated, Jaw widths: 36X41 mm



Order data

| | |
|--------------|---------------|
| Order number | 610950 36X41 |
| GTIN | 4045197441515 |
| Item class | 62A |

Description

Version:

Drop-forged. With close tolerance jaw widths.
With oval shaft.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome vanadium steel, chrome-plated.

Technical description

| | |
|----------------------|------------|
| Width across flats 2 | 41 mm |
| maximum jaw width b2 | 88 mm |
| maximum jaw width b1 | 80 mm |
| maximum jaw height h | 11 mm |
| Width across flats 1 | 36 mm |
| Width across flats | metric |
| Spanner length L | 358 mm |
| Standard | DIN 3110 |
| Standard | ISO 3318 |
| Jaw position 1 | 15 degrees |
| Jaw position 2 | 15 degrees |

| | |
|---|---------------|
| Surface | chrome plated |
| Product name attribute | chrome-plated |
| non-sparking | no |
| both sides have the same width across flats | no |
| Type of product | Spanner |