

**Velour-backed abrasive disc (A) 15 holes, Ø 150 mm, Grit: 600****Order data**

| | |
|--------------|---------------|
| Order number | 567790 600 |
| GTIN | 4045197526625 |
| Item class | 52M |

Description**Version:**

Velour-backed abrasive disc with **paper backing**. Dust-repellent coating prevents premature clogging. The back is covered with velour loops.

Velour-backed abrasive disc with semi-open distribution, aluminium oxide (A).

Application:

On **orbital sanders** with hook and loop pads e.g.No. 567990 (dust extraction available).

Universal **all-round product** for coarse, intermediate and fine abrasion on all metal and plastic surfaces, paint systems and woods.

maximum circumferential speed: 40 m/s

Technical description

| | |
|-----------------------------------------|---------|
| Grit | 600 |
| Disc Ø | 150 mm |
| Grinding medium code | A |
| Iron, sulphur and chlorine constituents | < 0.1 % |

| | |
|---------------------------------|-----------------------------|
| Product name attribute | Ø 150 mm |
| Number of dust extraction holes | 15 |
| Propulsive equipment | Orbital sander |
| maximum circumferential speed | 40 m/s |
| Type of product | Velour-backed abrasive disc |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|-------------------------------------------|----------------|----------|
| Alu Mg | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable only under restricted conditions | | |
| INOX | suitable | | |
| Ti | suitable only under restricted conditions | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable | | |
| Paint | suitable | | |
| Uni | suitable | | |
| dry | suitable | | |

Accessories

| | |
|------------------------------------------------|------------|
| PU hook and loop backing pad External Ø 150 mm | 567885 150 |
| Multi-hole PU backing pad External Ø 147 mm | 567990 147 |
| | 567887 150 |

PU hook and loop backing pad Multiple holes Outer Ø 150 mm
