

**Double open ended spanner DIN 895, Widths across flats: 27X32mm****Order data**

Order number	613000 27X32
GTIN	4045197384621
Item class	62A

Description**Version:**

Drop forged, jaw angle 15°, strong shaft.

Standard:

DIN 895

Material:

Special steel (strength 1200 – 1400 N/mm²).

Black oxidised finish.

Technical description

maximum jaw height h	12.5 mm
Width across flats 1	27 mm
Width across flats 2	32 mm
Width across flats	metric
Spanner length L	285 mm
Standard	DIN 895
Jaw position 1	15 degrees
Jaw position 2	15 degrees
Material	Special steel
Surface	burnished
Type of product	Spanner

