

HOLEX**Heavy-duty side cutter, bright finish, with grips, overall length: 180mm**

Order data

| | |
|--------------|---------------|
| Order number | 723395 180 |
| GTIN | 4045197887436 |
| Item class | 72B |

Description

Version:

Heavy-duty head with additionally induction hardened cutting edges (approx. 64 HRC). Laid-on joint. High cutting performance due to optimum leverage. Jaws bright finished, handles with multi-component covering.

Application:

For all types of wire (long working life even with hard wire). Heavy duty for the most demanding applications.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

| | |
|-------------------------------------|---------------------------|
| overall length | 180 mm |
| Cutting capacity piano wire up to Ø | 2.2 mm |
| Cutting capacity soft wire up to Ø | 3.8 mm |
| Cutting capacity hard wire up to Ø | 2.7 mm |
| Standard | DIN ISO 5749 |
| Handle | Multi-component covering |
| Manufacturing process | drop forged, oil-hardened |
| Material | Chrome vanadium steel |

| | |
|-----------------|----------------|
| Surface | bright finish |
| Type of product | Cutting pliers |