



Combination spanner, chrome-plated, Width across flats: 30mm



Order data

Order number	613950 30
GTIN	4045197159908
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw width.
With oval shaft.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome vanadium steel, chrome-plated.

Technical description

maximum jaw height h1	14 mm
Width across flats	30 mm
Spanner length L	340 mm
Width across flats	metric
maximum ring height $h_{2\max}$	20 mm
Standard	DIN 3113 A
Standard	ISO 3318
Standard	ISO 7738
Ring setting	15 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel

Surface	chrome plated
Product name attribute	chrome-plated
Type of product	Spanner