

Garant**Open ended spanner / ratchet ring spanner, Width across flats: 13mm****Order data**

Order number	614800 13
GTIN	4045197160232
Item class	61B

Description**Version:**

Drop forged. Ring end with especially smooth-running reversible ring ratchet.
Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 180 mm

Jaw width b: 27.1 mm

Jaw height h_1 : 6 mm

Ring thickness h_2 : 9.3 mm

Ring Ø D: 25.5 mm

Ratchet torque rating: 115 N·m

Technical description

Ring Ø D	25.5 mm
Jaw height h_1	6 mm
Width across flats	13 mm
Ratchet torque rating	115 N·m
Jaw width b	27.1 mm
Spanner length L	180 mm
Ring thickness h_2	9.3 mm
Width across flats	metric
Ring setting	0°

No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner

Accessories

Adapter for ratchet ring spanner Type 2	614850 2
---	----------