

**Garant****Open ended spanner / ratchet ring spanner short version, Width across flats: 19mm**

## Order data

|              |               |
|--------------|---------------|
| Order number | 614816 19     |
| GTIN         | 4045197199218 |
| Item class   | 61B           |

## Description

**Version:**

Drop forged. Ring end with especially smooth-running, robust ring ratchet. Extremely small working arc of 5°.

**Material:**

Chrome vanadium steel, matt chrome-plated.

## Technical description

|                               |             |
|-------------------------------|-------------|
| Spanner length L              | 137 mm      |
| Ring Ø D                      | 34.5 mm     |
| Width across flats            | 19 mm       |
| Jaw height h <sub>1</sub>     | 8.5 mm      |
| Ring thickness h <sub>2</sub> | 11.5 mm     |
| Jaw width b                   | 40.3 mm     |
| Width across flats            | metric      |
| Ring setting                  | 0 degrees   |
| No. of teeth                  | 72          |
| Working arc                   | 5 degrees   |
| Manufacturing process         | drop forged |

|                 |                       |
|-----------------|-----------------------|
| Material        | Chrome vanadium steel |
| Surface         | matt chrome-plated    |
| Type of product | Spanner               |

---

## Accessories

|                                         |          |
|-----------------------------------------|----------|
| Adapter for ratchet ring spanner Type 3 | 614850 3 |
|-----------------------------------------|----------|