

**Flap wheel roller, fleece (A) / fabric (A), Ø 100 × 50 mm, Grit equivalent: 80CRS****Order data**

Order number	568472 80CRS
GTIN	4045197924575
Item class	52E

Description**Version:**

Standard size Ø 100×100 mm or narrow version Ø 100×50 mm for grinding smaller areas.

Mounting bore Ø 19 mm with multiple splines.

Combination of **abrasive fabric and fleece**.

Application:

Finish similar to 80 / 120 grit flap strips, can also be used for **removing scratches** or for **applying a matt strip finish**.

Note:

For matching the width of narrow rollers Ø 100×50 mm use the spacer ring pack No. 568439.

Technical description

Grit equivalent	80
recommended speed	2800 min ⁻¹
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %

Roller Ø	100 mm
Roller width	50 mm
Product name attribute	Ø 100 × 50 mm
Type of product	Abrasive flap wheel roller, fleece

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Paint	suitable only under restricted conditions		
dry	suitable		