

Garant**Circular saw blade, wood, alternating teeth coarse, Blade Ø D: 300mm****Order data**

Order number	584015 300
GTIN	4045197220714
Item class	51S

Description**Version:**

Tipped with carbide inserts, precision version with high-strength blade, noise damped. Generously dimensioned carbide teeth allow multiple re-grinding.

Application:

For circular, cross-cut, compound, and mitre saws.

Type LWZ for longitudinal and cross cuts in all **natural woods and wooden sheet materials**.

Note:

Further circular saw blades can be found in Group 17.

Bore Ø: 30 mm

Drive holes number/Ø/pitch circle: 2/7/42 and 2/9/46 and 2/10/60 mm

Number of teeth: 28

Width of cut B: 3.2 mm

Technical description

Bore Ø	30 mm
Number of teeth	28

Blade Ø D	300 mm
Width of cut B	3.2 mm
Drive holes number/Ø/pitch circle	2/7/42 and 2/9/46 and 2/10/60 mm
Type of product	Circular saw blade