Garant

Circular saw blade, wood, alternating teeth coarse, Blade ⌀ D: 315mm

Order data

Order number	584015 315
GTIN	4045197220721
Item class	51S

Description

Version:
Tipped with carbide inserts, precision version with high-strength blade, noise damped.
Generously dimensioned carbide teeth allow multiple re-grinding.
Application:
For circular, cross-cut, compound, and mitre saws.
Type LWZ for longitudinal and cross cuts in all **natural woods and wooden sheet materials.**
Note:
Further circular saw blades can be found in Group 17.
Bore ⌀: 30 mm
Drive holes number/⌀/pitch circle: 2/7/42 and 2/9/46 and 2/10/60 mm
Number of teeth: 28
Width of cut B: 3.2 mm

Technical description

Blade ⌀ D	315 mm
Number of teeth	28

Bore ∅	30 mm
Width of cut B	3.2 mm
Drive holes number/∅/pitch circle	2/7/42 and 2/9/46 and 2/10/60 mm
Type of product	Circular saw blade