

Garant**Circular saw blade, wood, alternating teeth medium, Blade Ø D: 315mm**

Order data

Order number	584035 315
GTIN	4045197220783
Item class	51S

Description

Version:

Tipped with carbide inserts, precision version with high-strength blade, noise damped. Generously dimensioned carbide teeth allow multiple re-grinding.

Application:

For circular, cross-cut, compound, and mitre saws.

Type UW for **board materials, veneered or plastic coated on one side**, veneer packs longitudinally, hard paper and hard fabric.

Note:

Further circular saw blades can be found in Group 17.

Bore Ø: 30 mm

Drive holes number/Ø/pitch circle: 2/7/42 and 2/9/46 and 2/10/60 mm

Number of teeth: 48

Width of cut B: 3.2 mm

Technical description

Blade Ø D	315 mm
Bore Ø	30 mm

Number of teeth	48
Width of cut B	3.2 mm
Drive holes number/Ø/pitch circle	2/7/42 and 2/9/46 and 2/10/60 mm
Type of product	Circular saw blade