

**Double-ended ring spanner, deeply cranked, chrome-plated, Width across flats: 12X13mm****Order data**

Order number	615950 12X13
GTIN	4045197160959
Item class	62A

Description**Version:**

Drop-forged. With close tolerance jaw widths.
With oval shaft.

Standard:

DIN 838 / ISO 3318

Material:

Chrome vanadium steel, chrome-plated.

Technical description

Width across flats 1	12 mm
Spanner length L	216 mm
Width across flats 2	13 mm
maximum ring Ø D ₁ max	20 mm
maximum ring Ø D ₂ max	21 mm
Width across flats	metric
Surface	chrome plated
Product name attribute	chrome-plated
Type of product	Spanner

